

AIRFLOW AND FIELD WIRING DIAGRAM

STAND-ALONE FUME HOOD FACE VELOCITY CONTROL WITH ZONE PRESENCE SENSOR

1/4" PNEUMATIC TUBING FURNISHED, INSTALLED AND TERMINATED BY ATC

2 CONDUCTOR CABLE FURNISHED, INSTALLED AND TERMINATED BY ATC

TWISTED SHIELDED PAIR FURNISHED, INSTALLED, AND TERMINATED BY ATC

3 CONDUCTOR SHIELDED CABLE FURNISHED, INSTALLED, AND TERMINATED BY ATC

4 CONDUCTOR SHIELDED CABLE FURNISHED, INSTALLED AND TERMINATED BY ATC

6 CONDUCTOR SHIELDED CABLE FURNISHED, INSTALLED, AND TERMINATED BY ATC

10 CONDUCTOR SHIELDED CABLE FURNISHED, INSTALLED, AND TERMINATED BY ATC

ENVIROTRAK CONTROL PANELS REQUIRE 1200R 24 VAC BY OTHERS.

SUBMITTAL COPY

LABORATORY CONTROL SYSTEMS INC 91 Quinton Road Scott Township, PA 18447 (570) 487-2490 WebLab10 Date: 01/20/20

LABORATORY
STAND-ALONE FUME HOOD FACE VELOCITY CONTROL
WITH ZONE PRESENCE SENSOR

JOB NUMBER SHEET NO. OF